


YGHHC34C26

by Burndy
Catalog ID: YGHHC34C26

Prop 65 Notice

Compression ground connector, Material: Copper, Range Run: 300 Kcmil-500 Kcmil or 3/4" Rod, Tap: 6 SOL-2/O STR

Irreversible compression ground tap figure C connector. Accomadates all cable combinations from #6 solid through 500 kcmil



Product Details

General

Application	Cable to Cable or Cable to Ground Rod Applications
Connector Type	Tap
Construction Material - Main	Copper
Die Index	1011
Material	Copper
Plated	N
Sub Brand	Connector
Trade Name	HYTAP™
Type	Taps
UPC	621945456259
UPC 12 Digit	6219454562599

Dimensions

Width	2.13 in
-------	---------

Conductor Related

Conductor - Copper Solid Tap Range	6 Solid - 2/O Solid
Conductor - Copper Str Run Range	300 - 500 kcmil
Conductor - Copper Str Tap Range	6 Stranded - 2/O Stranded
Conductor - Rod Run Range	3/4" Rod

Certifications and Compliance

Certification - CSA Approved	[Delete]
Certification - UL Listed Direct Burial	Yes

Industry Standard(s)	<ul style="list-style-type: none"> • UL 467 • IEEE 837 • IEEE 837 2014 Qualified • UL 486A-486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837 • IEEE 837 2014 Qualified • UL 486A-486B
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)