

YGHP2C2

by Burndy
Catalog ID: YGHP2C2

Prop 65 Notice

Cu Compression Ground Tap Connector, #6 Sol- #2 Str(Run & Tap).

Features: Irreversible Compression Ground Tap Figure 6 Can Be Used As A Tap Connector Or As A Tap Splice Connector, Four Die Sets And Eight Connectors Can Accommodate A Conductor Range From #8 AWG Solid Through 500 KCMIL Plus 1/2 , 5/8 And 3/4 IN Copper Bonded Ground Rods, UL467 Listed, Acceptable For Direct Burial In Earth And Concrete, Prefilled With PENETROX Compound And Strip Sealed, Die Index: O Element A, Tools, Die Set Catalog Number, And (number Of Crimps): HYPRESS: Y35, Y39, Y750 Tool, U0 Die, (1), Y45 Tool, U0 Die With PT6515 Adapter, (1), Y46 Tool, U0 Die With PUADP-1 Adapter, (1), PAT750-18V Tool, U0 Die, (1), Conductor Type: Run: Commercial Stranded Copper, Tap: Commercial Stranded Copper, Shape: 6, Conductor Size (tap Range): 6 - 2 AWG, Conductor Size (run - Range): 6 - 2 AWG



Product Details

General

Application	For Direct Burial In Earth And Concrete
Connector Type	Tap
Die Index	O
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	781810220917
UPC 12 Digit	7818102209177

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in

Conductor Related

Conductor - Copper Solid Run	6
Conductor - Copper Solid Run Range	6
Conductor - Copper Solid Tap	6
Conductor - Copper Solid Tap Range	6
Conductor - Copper Str Run	6;5;4;3;2
Conductor - Copper Str Run Range	6-2
Conductor - Copper Str Tap	6;5;4;3;2

Conductor - Copper Str Tap Range	6-2
----------------------------------	-----

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837 • IEEE 837 2014 Qualified
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)