

YGHP34C26TN

by Burndy
Catalog ID: YGHP34C26TN

Prop 65 Notice

Tin plated Cu Compression Ground Rod Connector, 250- 500 kcmil , 5/8" to 3/4" Rod, 5/8" to 3/4" Rebar (Run) to 1/0 str to 2/0 str (Tap)



Product Details

General

Connector Type	Tap
Die Index	998
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAP™
Type	Taps
UPC	781810203965
UPC 12 Digit	7818102039655

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Length Overall inch	2.58 in

Conductor Related

Conductor - Copper Str Run	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Tap	1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	1/0-2/0
Conductor - Rebar Run	5 ;6
Conductor - Rebar Run Range	5 -6
Conductor - Rod Run	5/8 in;3/4 in
Conductor - Rod Run Range	5/8 in-3/4 in

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)