

# YGHP34C29TN

by Burndy  
Catalog ID: YGHP34C29TN

Prop 65 Notice

Tin plated Cu Compression Ground Rod Connector, 250- 500 kcmil ,  
5/8"- 3/4" Rod, 5/8" to 3/4 " Rebar (Run) to 3/0 str to 250 kcmil (Tap)



## Product Details

### General

Connector Type	Tap
Die Index	998
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAP™
Type	Taps
UPC	781810203958
UPC 12 Digit	7818102039588

### Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Length Overall inch	2.58 in

### Conductor Related

Conductor - Copper Str Run	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Tap	3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Tap Range	3/0-250
Conductor - Rebar Run	5 ;6
Conductor - Rebar Run Range	5 -6
Conductor - Rod Run	5/8 in;3/4 in
Conductor - Rod Run Range	5/8 in-3/4 in

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none"><li>• UL467</li><li>• IEEE 837</li></ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)