



## YGHP58C2W2TN

by Burndy  
Catalog ID: YGHP58C2W2TN

Compression Ground Tap Connector

### Product Details

#### General

Die Index	997
Material	Copper
Plated	Y
Plating Type	Tin Plated
Type	Taps
UPC	781810058213

#### Dimensions

Dimension - B Length inch	1.90 in
Dimension - Ground Rod Size	1/2 in - 5/8 in
Dimension - Width inch	0.75 in
Dimension - Width mm	19.1 mm

#### Conductor Related

Conductor - Copper Solid Tap Range	#6 - #2 Solid
Conductor - Rod Tap Range	1/2" to 5/8"
Conductor Range	#6 AWG (Sol) - #2 AWG (Sol)

#### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>UL467</li> <li>IEEE 837</li> <li>IEEE 837 2014 Qualified</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

#### Logistics

Minimum Pack Quantity
-----------------------

1
---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)