

YGHR26C12

by Burndy
Catalog ID: YGHR26C12

Prop 65 Notice

High Strength Irreversible Compression Ground Rod Tap Connectors.



Product Details

General

Connector Type	Tap
Die Index	998;1012
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Precrimp Die	UPRECRIMP12
Prefilled Oxide Inhibitor	Y
Trade Name	HYTAIL™
Type	Taps
UPC	781810220702
UPC 12 Digit	7818102207022

Dimensions

Dimension - B Length fraction	22/25 in
Dimension - B Length inch	0.88 in
Dimension - Ground Rod Size	1/2
Dimension - Height fraction	1-47/50 in
Dimension - Height inch	1.94 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	2 AWG-2/0 AWG
Conductor - Rod Size	1/2 in
Conductor - Rod Size Range	1/2 in
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size A • Rod-Size B

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)