



YGHR29C34

by Burndy
Catalog ID: YGHR29C34

Prop 65 Notice

Copper Compression Connector, 4/0 AWG(Str)-250 kcmil, 3/4" Ground Rod.

Features: High Torque Strength Ground Rod Connectors, Accommodates A Wide Range Of Copper Conductors To Ground Rod, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Prefilled With PENETROX Compound And Strip Sealed, Ground Rod Size: 3/4 IN, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y39, Y750, PAT750 Tool, PU998 Die, (1), U1011 Die, (2), HYPRESS: Y45 Tool, PU998 Die With PT6515 Adapter, (1), S1012 Die, (2), Y46 Tool, PU998 Die With PUADP-1 Adapter, (1), P1011 Die, (2), Conductor Type: Stranded Copper, Shape: 8, Conductor Size (run - Range): 4/0 AWG - 250 KCMIL, Die Index: 998 Element A

Product Details

General

Application	For Direct Burial In Earth Or Concrete
Connector Type	Tap
Die Index	998;1012
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Precrimp Die	UPRECRIMP58
Prefilled Oxide Inhibitor	Y
Sub Brand	HYGROUND, HYTAIL
Trade Name	HYTAIL™
Type	Taps
UPC	781810220757
UPC 12 Digit	7818102207577

Dimensions

Dimension - B Length fraction	22/25 in
Dimension - B Length inch	0.88 in
Dimension - Ground Rod Size	3/4
Dimension - Height fraction	2-15/79 in
Dimension - Height inch	2.19 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

Conductor Related

Conductor - Copper Str Size	4/0 AWG;250 kcmil
-----------------------------	-------------------

Conductor - Copper Str Size Range	4/0 AWG-250 kcmil
Conductor - Rod Size	3/4 in
Conductor - Rod Size Range	3/4 in
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size A • Rod-Size B

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)