

# YGHR34C58

by Burndy  
Catalog ID: YGHR34C58

Prop 65 Notice

High Strength Irreversible Compression Ground Rod Tap Connectors.



## Product Details

### General

|  |               |
|--|---------------|
| Connector Type                                 | Tap           |
| Die Index                                      | 998;1012      |
| Material                                       | Copper        |
| Oxide Inhibitor Type                           | Penetrox E    |
| Physical Attribute - Number of Crimps Required | 1             |
| Plated   | N             |
| Plating Type                                   | Unplated      |
| Precrimp Die                                   | UPRECRIMP58   |
| Prefilled Oxide Inhibitor                      | Y             |
| Trade Name                                     | HYTAIL™       |
| Type   | Taps          |
| UPC  | 781810220771  |
| UPC 12 Digit                                   | 7818102207711 |

### Dimensions

|                                 |           |
|---------------------------------|-----------|
| Dimension - B Length fraction   | 22/25 in  |
| Dimension - B Length inch       | 0.88 in   |
| Dimension - Ground Rod Size     | 5/8       |
| Dimension - Height fraction     | 2-7/50 in |
| Dimension - Height inch         | 2.14 in   |
| Dimension - L Length Overall mm | 22 mm     |
| Dimension - Length Overall inch | 0.88 in   |

### Conductor Related

|                                   |   |
|-----------------------------------|---|
| Conductor - Copper Str Size       | 300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil   |
| Conductor - Copper Str Size Range | 300 kcmil-500 kcmil   |
| Conductor - Rod Size              | 5/8 in  |
| Conductor - Rod Size Range        | 5/8 in  |
| Conductor Type                    | <ul style="list-style-type: none"> <li>• CU C Str-Size A</li> <li>• Rod-Size B</li> </ul> |

### Certifications and Compliance

|   |   |
|---|---|
| Certification - CSA Approved            | No  |
| Certification - ETL                     | No  |
| Certification - UL Listed Direct Burial | Yes   |
| Certification - UL Recognized           | No  |
| Certification - cULus                   | No  |
| Industry Standard(s)                    | <ul style="list-style-type: none"> <li>• UL467</li> <li>• IEEE 837</li> </ul> |
| Standards - Industry Standards Met      | <ul style="list-style-type: none"> <li>• UL467</li> <li>• IEEE 837</li> </ul> |
| Standards - RoHS Compliance Status      | CM  |
| UL Listed                               | Yes   |

## Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 15 |
|-----------------------|----|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)