



YGHR4C34

by Burndy
Catalog ID: YGHR4C34

Prop 65 Notice

High Strength Irreversible Compression Ground Rod Tap Connectors.

Product Details

General

Connector Type	Tap
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYTAIL™
Type	Taps
UPC	781810423745
UPC 12 Digit	7818104237455

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size A • Rod-Size B
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)