



YGHR58C2W3

by Burndy
Catalog ID: YGHR58C2W3

Prop 65 Notice

High Strength Irreversible Compression Ground Rod Tap Connectors.

Product Details

General

Connector Type	Tap
Die Index	998;1011
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYTAIL™
Type	Taps
UPC	781810002179
UPC 12 Digit	7818100021799

Dimensions

Dimension - B Length fraction	1-17/50 in
Dimension - B Length inch	1.34 in
Dimension - D inch	0.88 in
Dimension - Ground Rod Size	5/8
Dimension - Pad Width inch	2.19 in

Conductor Related

Conductor - Copper Solid Tap	2 AWG
Conductor - Copper Solid Tap Range	2 AWG
Conductor - Rod Size	5/8 in
Conductor - Rod Size Range	5/8 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)