



YGHS26

by Burndy
Catalog ID: YGHS26

Prop 65 Notice

Heavy Duty Irreversible Compression Terminals, 1.89 in L.

Features: Heavy Duty HYLINK Ground Splice Designed Not Only To Carry Short Circuit Load, But To Also Withstand High Mechanical Stress, Each Conductor Element Has An Inspection Probe Hole And A Center Stop To Ensure Proper Cable Insertion, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, UL486A Listed, Prefilled With PENETROX Compound And Strip Sealed, Die Index: 15 Element A, Conductor Type: Stranded Copper, Tools, Die Set Catalog Number, And (number Of Crimps): HYPRESS: Y35, Y39, Y750, PAT750 Tool, U28RT Die, (1), Y45 Tool, U28RT Die With PT6515 Adapter, (1), Y46 Tool, U28RT Die With PUADP-1 Adapter, (1)

Product Details

General

Application	For Direct Burial In Earth Or Concrete
Connector Type	Splice
Die Index	15
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splices
UPC	781810220467
UPC 12 Digit	7818102204677

Dimensions

Dimension - B Length fraction	5/6 in
Dimension - B Length inch	0.83 in
Dimension - L Length Overall mm	48 mm
Dimension - Length Overall inch	1.89 in
Dimension - Outside Diameter inch	0.71 in

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • UL 486A-486B • IEEE 837
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • UL 486A-486B • IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)