

YGHS28TN

by Burndy
Catalog ID: YGHS28TN

Prop 65 Notice

Heavy Duty Irreversible Compression Terminals.



Product Details

General

Connector Type	Terminal
Die Index	17
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
Type	Splices
UPC	781810110737
UPC 12 Digit	7818101107377

Dimensions

Dimension - B Length fraction	1-1/6 in
Dimension - B Length inch	1.18 in
Dimension - L Length Overall mm	66 mm
Dimension - Length Overall inch	2.59 in
Dimension - Outside Diameter inch	0.89 in

Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • UL 486A-486B • IEEE 837

Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• UL 486A-486B• IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)