

# YGHS34TN

by Burndy  
Catalog ID: YGHS34TN

Heavy Duty Irreversible Compression Terminals.



## Product Details

### General

Connector Type	Terminal
Die Index	22
Material	Copper
Physical Attribute - Number of Crimps Required	3
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
Type	Splices
UPC	781810110713
UPC 12 Digit	7818101107133

### Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.48 in
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.19 in
Dimension - Outside Diameter inch	1.24 in

### Conductor Related

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL467</li> <li>• UL 486A-486B</li> <li>• IEEE 837</li> </ul>

Standards - Industry Standards Met	<ul style="list-style-type: none"><li>• UL467</li><li>• UL 486A-486B</li><li>• IEEE 837</li></ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)