

# YGIBGAUGE1

by Burndy  
Catalog ID: YGIBGAUGE1

I-Beam Magnetic Gauge, 6 IN L, 4 IN W



## Product Details

### General

Connector Type	Tap
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	GROUNDLINK™
Type	Taps
UPC	781810098356
UPC 12 Digit	7818100983566

### Conductor Related

Conductor Type	CU C Str-Size
----------------	---------------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>UL 486A-486B</li> <li>IEEE 837</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>UL 486A-486B</li> <li>IEEE 837</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)