

# YGIBW2810002N

by Burndy  
Catalog ID: YGIBW2810002N

Prop 65 Notice

I-Beam Connector W/ Wide Flange Beams For Cu Cable, # 2-4/0 AWG



## Product Details

### General

Connector Type	Tap
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	GROUNDLINK™
Type	Taps
UPC	781810208700
UPC 12 Digit	7818102087000

### Dimensions

Dimension - I Beam Thickness inch	1.000" -1.060"
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.00 in

### Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	2 AWG-4/0 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>UL467</li> <li>IEEE 837</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>UL467</li> <li>IEEE 837</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)