

YGIBW343382N

by Burndy
Catalog ID: YGIBW343382N

Prop 65 Notice

I-Beam Connector for Copper Cable, 2 AWG - 500 kcmil, i-Beam flange
Thickness: .250 IN to .338 IN



Product Details

General

Connector Type	Tap
I Beam Style	Wide Flange Beam (Flange Parallel)
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	GROUNDLINK™
Type	Taps
UPC	781810039373
UPC 12 Digit	7818100393733

Dimensions

Dimension - B Length fraction	6 in
Dimension - B Length inch	6.00 in
Dimension - I Beam Thickness Range inch	0.250;0.275;0.300;0.312
Dimension - I Beam Thickness inch	0.250" - 0.338"
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in

Conductor Related

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	250 kcmil-500 kcmil
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> UL467 IEEE 837

Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)