

# YGL34C29TN

by Burndy  
Catalog ID: YGL34C29TN

Prop 65 Notice

250-500 TO 2-250 GRD GRI



## Product Details

### General

Connector Type	Tap
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYGRID™
Type	Taps
UPC	781810110966
UPC 12 Digit	7818101109666

### Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - D inch	0.50 in
Dimension - L Length Overall mm	64 mm
Dimension - Length Overall inch	2.50 in
Dimension - Pad Width inch	2.09 in

### Conductor Related

Conductor - Copper Str Size A	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size A Range	250 kcmil-500 kcmil
Conductor - Copper Str Size B	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size B Range	2 AWG-250 kcmil
Conductor - Rebar Size A	5 ;6
Conductor - Rebar Size A Range	5 -6
Conductor - Rod Size A	5/8 in;3/4 in
Conductor - Rod Size A Range	5/8 in-3/4 in
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size A</li> <li>• CU C Str-Size A</li> <li>• Rod-Size A</li> <li>• Rebar-Size A</li> <li>• CU C Solid-Size B</li> <li>• CU C Str-Size B</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL467</li> <li>• IEEE 837</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL467</li> <li>• IEEE 837</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)