

YGL34C34TN

by Burndy
Catalog ID: YGL34C34TN

Prop 65 Notice

Cu Compression Ground Connector, Cable to Cable/ Cable to Rebar, 250 - 500 Kcmil (Run), 250 - 500 Kcmil (Tap), Tin Plated



Product Details

General

Connector Type	Tap
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYGRID™
Type	Taps
UPC	781810110959
UPC 12 Digit	7818101109599

Dimensions

Dimension - B Length fraction	1-1/9 in
Dimension - B Length inch	1.10 in
Dimension - D inch	0.75 in
Dimension - L Length Overall mm	75 mm
Dimension - Length Overall inch	2.94 in
Dimension - Pad Width inch	2.28 in

Conductor Related

Conductor - Copper Str Size A	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size A Range	250 kcmil-500 kcmil
Conductor - Copper Str Size B	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size B Range	250 kcmil-500 kcmil
Conductor - Rebar Size A	5 ;6
Conductor - Rebar Size A Range	5 -6
Conductor - Rod Size A	5/8 in;3/4 in
Conductor - Rod Size A Range	5/8 in-3/4 in
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size A • CU C Str-Size A • Rod-Size A • Rebar-Size A • CU C Solid-Size B • CU C Str-Size B

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)