

YGLR29C12

by Burndy
Catalog ID: YGLR29C12

Prop 65 Notice

Copper Compression Connector, Ground Rod to Grid, 2 AWG (Str.) to 250 kcmil, 1/2" Ground Rod or #3- #4 Rebar



Product Details

General

Connector Type	Tap
Die Index	997
Die Index - Element A	997
Die Index - Element B	1011
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Precrimp Die	UPRECRIMP12
Prefilled Oxide Inhibitor	Y
Trade Name	GRIDLOK™
Type	Taps
UPC	781810220801
UPC 12 Digit	7818102208011

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - D inch	0.31 in
Dimension - Ground Rod Size	1/2
Dimension - L Length Overall mm	64 mm
Dimension - Length BB inch	0.88 in
Dimension - Length Overall inch	2.53 in

Conductor Related

Conductor - Copper Str Size A	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size A Range	2 AWG-250 kcmil
Conductor - Rebar Tap	3;4
Conductor - Rod Size B	1/2 in
Conductor - Rod Size B Range	1/2 in

Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • Rod-Size • CU Weld C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)