

# YGLR29C34TN

by Burndy  
Catalog ID: YGLR29C34TN

Prop 65 Notice

Tin plated Copper Compression Connector, Ground Rod to Grid, 2 str to 250 kcmil, 3/4" Ground Rod or #5- #6 Rebar



## Product Details

### General

Connector Type	Tap
Die Index	997
Die Index - Element B	1011
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	GRIDLOK™
Type	Taps
UPC	781810131220
UPC 12 Digit	7818101312200

### Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - D inch	0.50 in
Dimension - Ground Rod Size	3/4
Dimension - L Length Overall mm	67 mm
Dimension - Length BB inch	0.88 in
Dimension - Length Overall inch	2.63 in

### Conductor Related

Conductor - Copper Str Size A	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size A Range	2 AWG-250 kcmil
Conductor - Rebar Tap	5;6
Conductor - Rod Size B	3/4 in
Conductor - Rod Size B Range	3/4 in
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• Rod-Size</li> <li>• CU Weld C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL467</li> <li>• IEEE 837</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
 47 East Industrial Park Drive  
 Manchester, New Hampshire 03109

**Customer Service Hours:**  
 8 AM - 8 PM Eastern Monday-Friday  
 Emergency Service 24-hours/365 Days  
 Phone: 1-800-346-4175  
 1-603-647-5299 (International)