

YGLR29C58TN

by Burndy
Catalog ID: YGLR29C58TN

Prop 65 Notice

Tin plated Copper Compression Connector, Ground Rod to Grid, 2 AWG (Str.) to 250 kcmil, 5/8" Ground Rod or #5- #6 Rebar



Product Details

General

Connector Type	Tap
Die Index	997
Die Index - Element B	1011
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	GRIDLOK™
Type	Taps
UPC	781810042878
UPC 12 Digit	7818100428788

Dimensions

Dimension - B Length fraction	22/25 in
Dimension - B Length inch	0.88 in
Dimension - Ground Rod Size	5/8
Dimension - Height fraction	2-7/50 in
Dimension - Height inch	2.14 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

Conductor Related

Conductor - Copper Str Size A	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size A Range	2 AWG-250 kcmil
Conductor - Rebar Tap	5;6
Conductor - Rod Size B	5/8 in
Conductor - Rod Size B Range	5/8 in
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • Rod-Size • CU Weld C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)