

YGLR34C58TN

by Burndy
Catalog ID: YGLR34C58TN

Prop 65 Notice

Tin plated Copper Compression Connector, Ground Rod to Grid, 250 kcmil - 500 kcmil, 5/8" Ground Rod or #5- #6 Rebar



Product Details

General

Connector Type	Tap
Die Index	1011
Die Index - Element B	1011
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	GRIDLOK™
Type	Taps
UPC	781810416280
UPC 12 Digit	7818104162800

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - D inch	0.31 in
Dimension - Ground Rod Size	5/8
Dimension - L Length Overall mm	64 mm
Dimension - Length BB inch	0.88 in
Dimension - Length Overall inch	2.53 in

Conductor Related

Conductor - Copper Str Size A	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size A Range	250 kcmil-500 kcmil
Conductor - Rebar Tap	5;6
Conductor - Rod Size B	5/8 in
Conductor - Rod Size B Range	5/8 in
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • Rod-Size • CU Weld C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)