

YGS26

by Burndy
Catalog ID: YGS26

Prop 65 Notice

Grounding Irreversible Compression Splices.

Features: Irreversible Compression HYLINK Ground Splices Specifically Designed For Grounding Applications, Each Conductor Element Has An Inspection Probe Hole And A Center Stop To Ensure Proper Cable Insertion, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, UL486A Listed, Prefilled With PENETROX Compound And Strip Sealed, Die Index: 13 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD7-34R, OUR840 Tool, W26VT, X26RT Die, (4), Hydraulic: Y35, Y39, Y750, PAT750 Tool, U26RT Die, (2), Y45 Tool, U26RT Die With PT6515 Adapter, Y46 Tool, U26RT Die With PUADP-1 Adapter, (2), Conductor Type: Stranded Copper



Product Details

General

Application	For Direct Burial In Earth Or Concrete
Connector Type	Splice
Construction Material - Main	Copper
Die Index	13
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YGS, Grounding Irreversible
UPC	781810220412
UPC 12 Digit	7818102204122

Dimensions

Dimension - B Length fraction	1-10/27 in
Dimension - B Length inch	1.45 in
Dimension - L Length Overall mm	80 mm
Dimension - Length Overall inch	3.13 in
Dimension - Outside Diameter inch	0.56 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	2/0 Str.
Conductor - Copper Str Size Range	2/0 Str.
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • UL 486A-486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A-486B • UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)