

YGS29

by Burndy
Catalog ID: YGS29

Prop 65 Notice

Grounding Irreversible Compression Splices.



Product Details

General

Connector Type	Splice
Die Index	16
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Trade Name	HYLINK™
Type	Splices
UPC	781810220436
UPC 12 Digit	7818102204366

Dimensions

Dimension - B Length fraction	1-4/7 in
Dimension - B Length inch	1.57 in
Dimension - L Length Overall mm	86 mm
Dimension - Length Overall inch	3.37 in
Dimension - Outside Diameter inch	0.75 in

Conductor Related

Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> UL467 UL 486A-486B

Standards - Industry Standards Met	<ul style="list-style-type: none">• UL 486A-486B• UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)