

# YGS8C

by Burndy  
Catalog ID: YGS8C

Prop 65 Notice

Grounding Irreversible Compression Splices.



## Product Details

### General

Color Code	Red
Connector Type	Splice
Die Index	49
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Trade Name	HYLINK™
Type	Splices
UPC	781810102503
UPC 12 Digit	7818101025033

### Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.78 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	0.27 in

### Conductor Related

Conductor - Copper Solid Size	8
Conductor - Copper Solid Size Range	8
Conductor - Copper Str Size	8 Sol./Str.
Conductor - Copper Str Size Range	8 Sol./Str.
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL467</li> <li>• UL 486A-486B</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL 486A-486B</li> <li>• UL467</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)