

YGT275WOCC

by Burndy
Catalog ID: YGT275WOCC

Static Grounding Receptacle without cap to provide permanent corrosion proof grounding point using suitable YGHR or YGLR or YGHP connectors.



Product Details

General

Connector Type	To be connected to suitable YGHR or YGLR or YGHP
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYGROUND®
UPC	781810096055
UPC 12 Digit	7818100960555

Dimensions

Dimension - D inch	2.75 in
Dimension - Ground Rod Size	3/4
Dimension - Height fraction	5-1/2 in
Dimension - Height inch	5.50 in

Conductor Related

Conductor - Rod Size	3/4 in
Conductor - Rod Size Range	3/4 in
Conductor Type	Rod-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)