

# YGT275

by Burndy  
Catalog ID: YGT275

Static Grounding Receptacle to provide permanent corrosion proof grounding point using suitable YGHR or YGLR or YGHP connectors.



## Product Details

### General

Connector Type	To be connected to suitable YGHR or YGLR or YGHP
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYGROUND®
UPC	781810002148
UPC 12 Digit	7818100021488

### Dimensions

Dimension - D inch	2.75 in
Dimension - Ground Rod Size	3/4
Dimension - Height fraction	5-1/2 in
Dimension - Height inch	5.50 in

### Conductor Related

Conductor - Rod Size	3/4 in
Conductor - Rod Size Range	3/4 in
Conductor Type	Rod-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)