



YH2929WCC

by Burndy
Catalog ID: YH2929WCC

Prop 65 Notice

Cu-code-H-Tap Crimpit, 250-2(4/0-2)(Main) ,250-2(4/0-2)(Tap 1), Flame retardent.

Features: Accommodates A Wide Range Of Run/Tap Copper Cable Combinations Including Both Flexible And Code Combinations, All (B/B, B/I, I/B, I/I) Combinations Acceptable: Each Connector Has Many Copper Cable Combination Applications Allowing Maximum Flexibility For The Design And Installation Of A System, Tap Grooves Function Independently Of Each Other, Use Of One Tap Is Required, Balance May Be Used Or Left Empty: Provides Maximum Design And Installation Flexibility, Color Code On The Connector Matches Installation Die: Provides Matched System For Fast And Easy Installation, Die Index Embossed On Connector After Completion Of Crimp: Permanent Inspectability Of Installed Connectors To Insure Consistently Reliable And Dependable Connections, Recommended Flame Retardant Type CFFR Insulating Covers Meet Oxygen Index 28 And UL94 V-O Requirements: A Complete Insulated UL Listed Installation Is Provided, Third Hand Constrains Conductors While Installer Completes Crimp, Included With Each Connector, Simplifies Installation, Reducing Installed Cost, Use PUADP-1 Adaptor With U Dies In Y46, Color Code: Purple, Tools, Die Set Catalog Number, And (number Of Crimps): Y750 Tool, U654 Die, (1), Y46 Tool, U654 Die With PUADP-1 Adapter, (1), P654 Die, (1), Flame Retardant Cover: CFD-FR, Wire Strip Length: 1-1/16 IN, Cover Packaged With Connector: Yes, Die Index: 654 Element A, Conductor Type: Run: Commercial Stranded Copper, Flexible Copper, Tap: Commercial Stranded Copper, Flexible Copper, Conductor Size (run - Range): 2 AWG - 250 KCMIL, Conductor Size (tap Range): 2 AWG - 250 KCMIL, Shape: H

Product Details

General

Application	For Used To Accommodates A Wide Range Of Run/Tap Copper Cable Combinations Including Both Flexible And Code Combinations
Color Code	Purple
Connector Type	H-Tap
Die Index	654
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810436424
UPC 12 Digit	7818104364244

Dimensions

Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.90 in
Dimension - Strip Length inch	1-1/16

Dimension - Width inch	1.85 in
------------------------	---------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Run	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex G Tap	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex H Tap	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex I Run	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0
Conductor - Copper Flex I Tap	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex K Run	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex K Tap	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex M Run	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex M Tap	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Str Run	2;1;1/0;2/0;3/0;4/0;250
Conductor - Copper Str Tap	2;1;1/0;2/0;3/0;4/0;250

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)