



YH4434WCC

by Burndy
Catalog ID: YH4434WCC

Prop 65 Notice

Copper Compression Crimpit H Tap With Clear Flame Retardant Cover,
1000-750 KCMIL (Run), 1000-750 KCMIL (Tap), White

Product Details

General

| | |
|--------------------|----------------------|
| Color Code | Yellow |
| Connector Type | H-Tap |
| Die Index | KR |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Temperature Rating | 194 |
| Trade Name | CRIMPIT™ |
| Type | Compression Taps |
| UPC | 781810438299 |
| UPC 12 Digit | 7818104382999 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - L Length Overall mm | 25 mm |
| Dimension - Length Overall inch | 1.00 in |
| Dimension - Strip Length inch | 1-3/8 |
| Dimension - Width inch | 3.50 in |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-------------------------------|-----------------|
| Conductor - Copper Flex G Run | 500;600;700 |
| Conductor - Copper Flex G Tap | 350 |
| Conductor - Copper Flex H Tap | 350 |
| Conductor - Copper Flex I Run | 500;550;600;700 |
| Conductor - Copper Flex I Tap | 350 |
| Conductor - Copper Flex K Run | 500;600;700 |
| Conductor - Copper Flex K Tap | 350 |

| | |
|-------------------------------|--------------------------|
| Conductor - Copper Flex M Run | 500;600;700 |
| Conductor - Copper Flex M Tap | 350 |
| Conductor - Copper Str Run | 700;750;800;850;900;1000 |
| Conductor - Copper Str Tap | 350;400;450;500 |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 5 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)