



## YH4434WC

by Burndy  
Catalog ID: YH4434WC

Prop 65 Notice

Cu H-Tap Connector, 1000-750 kcmil, 777-750 kcmil Flex, 500-350 Kcmil, 350 kcmil Flex, Tin plated

## Product Details

### General

Color Code	Yellow
Connector Type	H-Tap
Die Index	KR
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Compression Taps
UPC	781810418925
UPC 12 Digit	7818104189255

### Dimensions

Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in
Dimension - Strip Length inch	1-3/8
Dimension - Width inch	3.50 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex G Run	500;600;700
Conductor - Copper Flex G Tap	350
Conductor - Copper Flex H Tap	350

Conductor - Copper Flex I Run	500;550;600;700
Conductor - Copper Flex I Tap	350
Conductor - Copper Flex K Run	500;600;700
Conductor - Copper Flex K Tap	350
Conductor - Copper Flex M Run	500;600;700
Conductor - Copper Flex M Tap	350
Conductor - Copper Str Run	700;750;800;850;900;1000
Conductor - Copper Str Tap	350;400;450;500

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	Yes

### Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)