



YH6C6CWC

by Burndy
Catalog ID: YH6C6CWC

Prop 65 Notice

Cu H-Tap Crimpit W/Black Cover Kit, 6-10 Code & Flex(Main), 6-14 Code & Flex(Tap), Tin Plated, Orange.

Features: Accommodates A Wide Range Of Run/Tap Copper Cable Combinations Including Both Flexible And Code Combinations, All (B/B, B/I, I/B, I/I) Combinations Acceptable: Each Connector Has Many Copper Cable Combination Applications Allowing Maximum Flexibility For The Design And Installation Of A System, Tap Grooves Function Independently Of Each Other, Use Of One Tap Is Required, Balance May Be Used Or Left Empty: Provides Maximum Design And Installation Flexibility, Color Code On The Connector Matches Installation Die: Provides Matched System For Fast And Easy Installation, Die Index Embossed On Connector After Completion Of Crimp: Permanent Inspectability Of Installed Connectors To Insure Consistently Reliable And Dependable Connections, Recommended Flame Retardant Type CFFR Insulating Covers Meet Oxygen Index 28 And UL94 V-O Requirements: A Complete Insulated UL Listed Installation Is Provided, Third Hand Constrains Conductors While Installer Completes Crimp, Included With Each Connector, Simplifies Installation, Reducing Installed Cost, Use PUADP-1 Adaptor With U Dies In Y46, Cover Packaged With Connector: Yes, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, UBGRT Die, (1), Y46 Tool, UBGRT Die With PUADP-1 Adapter, (1), Flame Retardant Cover: CFBG-FR, Color Code: Orange, Die Index: GRT Element A, Wire Strip Length: 3/4 IN, Conductor Size (run - Range): 10 - 6 AWG, Conductor Type: Run: Commercial Stranded Copper, Flexible Copper, Tap: Commercial Stranded Copper, Flexible Copper, Shape: H, Conductor Size (tap Range): 14 - 6 AWG

Product Details

General

Application	For Used To Accommodates A Wide Range Of Run/Tap Copper Cable Combinations Including Both Flexible And Code Combinations
Sub Brand	CRIMPIT
Type	Compression Taps
UPC	781810051047

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)

