

YHD200J1444

by Burndy
Catalog ID: YHD200J1444

Prop 65 Notice

HYCRIMP™ STIRRUP.



Product Details

General

Connector Type	H-Tap
Die Index	D3
Material	Aluminum
Material - Bail	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYCRIMP™
Type	Bail
UPC	781810054215
UPC 12 Digit	7818100542155

Dimensions

Dimension - B Length fraction	1-22/25 in
Dimension - B Length inch	1.88 in
Dimension - D inch	3.00 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.0 in
Dimension - Pad Width inch	5.00 in

Conductor Related

Conductor - ACSR Str Size	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG-2/0 (6/1) Quail AWG
Conductor - AL Str Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Size Range	2/0 AWG-4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)