

# YHD300J1496

by Burndy  
Catalog ID: YHD300J1496

Prop 65 Notice

HYCRIMP™ STIRRUP.



## Product Details

### General

Connector Type	H-Tap
Die Index	D3
Material	Aluminum
Material - Bail	Copper
Plated	Y
Plating Type	Tin
Type	Bail
UPC	781810171257
UPC 12 Digit	7818101712577

### Dimensions

Dimension - B Length fraction	1-22/25 in
Dimension - B Length inch	1.88 in
Dimension - D inch	4.75 in
Dimension - L Length Overall mm	394 mm
Dimension - Length Overall inch	15.5 in
Dimension - Pad Width inch	5.00 in

### Conductor Related

Conductor - ACSR Str Size	1 (6/1) Robin AWG;1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG
Conductor - ACSR Str Size Range	1 (6/1) Robin AWG-2/0 (6/1) Quail AWG
Conductor - AL Str Size	1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Size Range	1 AWG-4/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)