

YHD350J1496

by Burndy
Catalog ID: YHD350J1496

Prop 65 Notice

HYCRIMP™ STIRRUP.



Product Details

General

Connector Type	H-Tap
Die Index	D3
Material	Aluminum
Material - Bail	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYCRIMP™
Type	Bail
UPC	781810081167
UPC 12 Digit	7818100811677

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.50 in
Dimension - D inch	4.75 in
Dimension - L Length Overall mm	394 mm
Dimension - Length Overall inch	15.5 in
Dimension - Pad Width inch	5.00 in

Conductor Related

Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG-4/0 (6/1) Penquin AWG
Conductor - AL Str Size	3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil
Conductor - AL Str Size Range	3/0 AWG-300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed

No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)