

# YHN600

by Burndy  
Catalog ID: YHN600

Compression Line Tap for Copper, AL or ACSR and Compact  
Conductors,wire diameter range,groove A(Run):0.57-0.81



## Product Details

### General

Die Index	N
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYCRIMP™
UPC	781810139608

### Dimensions

Dimension - Height fraction	2 in
Dimension - Height inch	2.00 in
Dimension - L Length Overall mm	89 mm
Dimension - Length Overall inch	3.50 in
Dimension - Width fraction	1-7/25 in
Dimension - Width inch	1.28 in
Dimension - Width mm	33 mm

### Conductor Related

Conductor - ACSR Cmpt Run	300 kcmil;556.5 kcmil
Conductor - ACSR Cmpt Run Range	300 kcmil-556.5 kcmil
Conductor - ACSR Cmpt Tap	300 kcmil;397 kcmil
Conductor - ACSR Cmpt Tap Range	300 kcmil-397 kcmil
Conductor - ACSR Str Run	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil;477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Run Range	266.8 (18/1) Waxwing kcmil-477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Tap	266.8 (18/1) Waxwing kcmil;300.0 (26/7) Ostrich kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Tap Range	266.8 (18/1) Waxwing kcmil-336.4 (18/1) Merlin kcmil
Conductor - AL Str Run	250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil
Conductor - AL Str Run Range	250 kcmil-500 kcmil

Conductor - AL Str Tap	250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Tap Range	250 kcmil-350 kcmil
Conductor - Copper Solid Tap	336-400
Conductor - Copper Solid Tap Range	336-400
Conductor - Copper Str Run	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Tap	250 - 350
Conductor - Copper Str Tap Range	250 - 350

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	50
-----------------------	----

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)