

# YHO100J1444

by Burndy  
Catalog ID: YHO100J1444

Prop 65 Notice

HYCRIMP™ STIRRUP.



## Product Details

### General

Connector Type	H-Tap
Die Index	O
Material	Aluminum
Material - Bail	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYCRIMP™
Type	Bail
UPC	781810035078
UPC 12 Digit	7818100350788

### Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - D inch	3.00 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.0 in
Dimension - Pad Width inch	5.00 in

### Conductor Related

Conductor - ACSR Str Size	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - AL Str Size Range	6 AWG-1 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)