

# YHSA10K10BF

by Burndy  
Catalog ID: YHSA10K10BF

Cu Heat Shrink Terminal, Block Fork, 10-12 AWG, #8-10 Stud, 1.27" L, 0.35" W, Brazed Seam, Tin Plated, Yellow(Insul Color).

Features: Made From Pure Copper, Annealed For Maximum Strength, Color-Coded, Imprinted With Wire Size, Serrated Barrels Offer Maximum Wire Contact And Tensile Strength, Electro Tin Plated For Corrosion Resistance, Wire Strip Length 5/16 IN, Finish: Electro-Tin Plated, Wire Strip Length: 5/16 IN



## Product Details

### General

|                                  |                             |
|----------------------------------|-----------------------------|
| Application                      | For Use On Copper Conductor |
| Connector Type                   | Terminal                    |
| Insulation                       | Y                           |
| Insulation Type                  | Heat shrink                 |
| Material                         | Copper                      |
| Physical Attribute - Tongue Type | Block Fork                  |
| Plated                           | Y                           |
| Plating Type                     | Tin                         |
| Sub Brand                        | HYDENT                      |
| Trade Name                       | HYDENT™                     |
| Type                             | YHS, Heat Shrink            |
| UPC                              | 781810524633                |
| UPC 12 Digit                     | 7818105246333               |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 32 mm    |
| Dimension - Length Overall inch | 1.27 in  |
| Dimension - Pad Width inch      | 0.35 in  |
| Dimension - Strip Length inch   | 11/32 in |
| Dimension - Stud Size inch      | #10      |
| Dimension - Z inch              | 0.29 in  |

### Conductor Related

|                                   |                  |
|-----------------------------------|------------------|
| Conductor - Copper Str Size Range | 12 str.- 10 str. |
| Conductor Type                    | CU C Str-Size    |

### Certifications and Compliance

|                               |    |
|-------------------------------|----|
| Certification - CSA Approved  | No |
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Certification - cULus         | No |

|                                    |    |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

## Logistics

|                       |        |
|-----------------------|--------|
| Carton Quantity       | 100 EA |
| Minimum Pack Quantity | 50     |

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)