

# YHSA10K10FRK

by Burndy  
Catalog ID: YHSA10K10FRK

Cu Heat Shrink Fork Tongue Terminal For 12 - 10 AWG and #10 Stud, Tin Plated



## Product Details

### General

Connector Type	Terminal
Insulation	Y
Insulation Type	Heat shrink
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810477359
UPC 12 Digit	7818104773599

### Dimensions

Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.16 in
Dimension - N inch	0.27 in
Dimension - Pad Width inch	0.37 in
Dimension - Strip Length inch	5/16 in
Dimension - Stud Size inch	#10

### Conductor Related

Conductor - Copper Str Size Range	12 str.- 10 str.
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	20
Packaging Type	Bag

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)