

YHSA10K10LF

by Burndy
Catalog ID: YHSA10K10LF



Cu Heat Shrink Terminal, Snap Fork Tongue, 10-12 AWG, #8-10 Stud, 1.27" L, 0.35" W, Tin Plated, Yellow(Insul Color).

Features: Made From Pure Copper, Annealed For Maximum Strength, Color-Coded, Imprinted With Wire Size, Serrated Barrels Offer Maximum Wire Contact And Tensile Strength, Electro Tin Plated For Corrosion Resistance, Wire Strip Length 5/16 IN, Finish: Electro-Tin Plated, Wire Strip Length: 5/16 IN

Product Details

General

Application	For Use On Copper Conductor
Connector Type	Terminal
Insulation	Y
Insulation Type	Heat shrink
Material	Copper
Physical Attribute - Tongue Type	Snap Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810524640
UPC 12 Digit	7818105246400

Dimensions

Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.27 in
Dimension - Pad Width inch	0.35 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size fraction	#10
Dimension - Stud Size inch	#8 - #10
Dimension - Z inch	0.29 in

Conductor Related

Conductor - Copper Str Size Range	12 str.- 10 str.
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)