



YHSA10K10RK

by Burndy
Catalog ID: YHSA10K10RK

Cu Heat Shrink Ring Tongue Terminal For 12 - 10 AWG and #10 Stud, Tin Plated

Product Details

General

Connector Type	Terminal
Insulation	Y
Insulation Type	Heat shrink
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810477298
UPC 12 Digit	7818104772988

Dimensions

Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Hole Size mm	4.00 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.18 in
Dimension - Pad Width inch	0.34 in
Dimension - Strip Length inch	5/16 in
Dimension - Stud Size inch	#10

Conductor Related

Conductor - Copper Str Size Range	12 str.- 10 str.
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	20
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)