

## YHSA10K12RK

by Burndy  
Catalog ID: YHSA10K12RK

Cu Heat Shrink Ring Tongue Terminal For 12 - 10 AWG and 1/2" Stud, Tin Plated



### Product Details

#### General

Connector Type	Terminal
Insulation	Y
Insulation Type	Heat shrink
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810477328
UPC 12 Digit	7818104773288

#### Dimensions

Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13.00 mm
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.36 in
Dimension - Pad Width inch	0.69 in
Dimension - Strip Length inch	5/16 in
Dimension - Stud Size inch	1/2 in

#### Conductor Related

Conductor - Copper Str Size Range	12 str.- 10 str.
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	20
Packaging Type	Bag

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)