



YHSA10K38RK

by Burndy
Catalog ID: YHSA10K38RK

Cu Heat Shrink Ring Tongue Terminal For 12 - 10 AWG and 3/8" Stud, Tin Plated

Product Details

General

| | |
|--------------------------------------|---------------|
| Connector Type | Terminal |
| Insulation | Y |
| Insulation Type | Heat shrink |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Ring |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | HYDENT™ |
| UPC | 781810477311 |
| UPC 12 Digit | 7818104773111 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - B Length fraction | 2/9 in |
| Dimension - B Length inch | 0.22 in |
| Dimension - Hole Size fraction | 2/5 |
| Dimension - Hole Size inch | 0.40 in |
| Dimension - Hole Size mm | 10.00 mm |
| Dimension - L Length Overall mm | 37 mm |
| Dimension - Length Overall inch | 1.45 in |
| Dimension - N inch | 0.28 in |
| Dimension - Pad Width inch | 0.56 in |
| Dimension - Strip Length inch | 5/16 in |
| Dimension - Stud Size inch | 3/8 in |

Conductor Related

| | |
|-----------------------------------|------------------|
| Conductor - Copper Str Size Range | 12 str.- 10 str. |
| Conductor Type | CU C Str-Size |

Certifications and Compliance

| | |
|------------------------------|----|
| Certification - CSA Approved | No |
|------------------------------|----|

| | |
|------------------------------------|----|
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|--------|
| Carton Quantity | 100 EA |
| Minimum Pack Quantity | 20 |
| Packaging Type | Bag |

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)