



## YHSA10K6

by Burndy  
Catalog ID: YHSA10K6

Cu Heat Shrink Terminal, Ring Tongue, 10-12 AWG, #4-6 Stud, 1.15" L, 0.34" W, Serrated bbl, Tin plated, Yellow(Insul Color).

Features: Made From Pure Copper, Annealed For Maximum Strength, Color-Coded, Imprinted With Wire Size, Serrated Barrels Offer Maximum Wire Contact And Tensile Strength, Electro Tin Plated For Corrosion Resistance, Wire Strip Length 5/16 IN, Finish: Electro-Tin Plated, Wire Strip Length: 5/16 IN, Package: 100/Bag

## Product Details

### General

Application	For Use On Copper Conductor
Connector Type	Terminal
Insulation	Y
Insulation Type	Heat shrink
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810524664
UPC 12 Digit	7818105246644

### Dimensions

Dimension - B Length inch	0.22 in
Dimension - Hole Size inch	0.14 in
Dimension - Hole Size mm	4 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.15 in
Dimension - N inch	0.17 in
Dimension - Pad Width inch	0.34 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#4 - #6
Dimension - Z inch	0.17 in

### Conductor Related

Conductor - Copper Str Size Range	12 str.- 10 str.
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

#### Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	50

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)