



YHSA10K8FRK

by Burndy
Catalog ID: YHSA10K8FRK

Cu Heat Shrink Terminal, Fork Tongue, 10-12 AWG, #6-8 Stud, 1.17" L, 0.35" W, Serrated bbl, Tin plated, Yellow(Insul Color)

Product Details

General

Connector Type	Terminal
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810511022
UPC 12 Digit	7818105110222

Dimensions

Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.17 in
Dimension - N inch	0.17 in
Dimension - Pad Width inch	0.35 in
Dimension - Strip Length inch	5/16 in
Dimension - Stud Size inch	#8

Conductor Related

Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)