



YHSA10K8

by Burndy
Catalog ID: YHSA10K8

Cu Heat Shrink Terminal, Ring Tongue, 10-12 AWG, #6-8 Stud, 1.15" L, 0.34" W, Serrated bbl, Tin plated, Yellow(Insul Color).

Features: Made From Pure Copper, Annealed For Maximum Strength, Color-Coded, Imprinted With Wire Size, Serrated Barrels Offer Maximum Wire Contact And Tensile Strength, Electro Tin Plated For Corrosion Resistance, Wire Strip Length 5/16 IN, Wire Strip Length: 5/16 IN, Finish: Electro-Tin Plated, Package: 100/Bag

Product Details

General

Application	For Use On Copper Conductor
Connector Type	Terminal
Insulation	Y
Insulation Type	Heat shrink
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810524701
UPC 12 Digit	7818105247011

Dimensions

Dimension - B Length inch	0.22 in
Dimension - Hole Size fraction	7/50
Dimension - Hole Size inch	0.14 in
Dimension - Hole Size mm	4.00 mm
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.14 in
Dimension - Pad Width inch	0.29 in
Dimension - Strip Length inch	5/16 in
Dimension - Stud Size inch	#6 - #8

Conductor Related

Conductor - Copper Str Size Range	12 str.- 10 str.
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)