

YHSA14K14FRK

by Burndy
Catalog ID: YHSA14K14FRK

Cu Heat Shrink Spade Terminal, Fork Tongue, 14-16 AWG, 1/4" Stud, 1.41" L, 0.47" W, Serrated bbl, Tin plated



Product Details

General

Connector Type	Terminal
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810511039
UPC 12 Digit	7818105110399

Dimensions

Dimension - L Length Overall mm	36 mm
Dimension - Length Overall inch	1.41 in
Dimension - N inch	0.17 in
Dimension - Pad Width inch	0.47 in
Dimension - Strip Length inch	5/16 in
Dimension - Stud Size inch	0.25

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)