

# YHSA14K14RK

by Burndy  
Catalog ID: YHSA14K14RK

Heat Shrink Ring Tongue Terminal For 16 - 14 AWG and 1/4 Stud.



## Product Details

### General

Connector Type	Terminal
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810477274
UPC 12 Digit	7818104772744

### Dimensions

Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.26 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	36 mm
Dimension - Length Overall inch	1.40 in
Dimension - N inch	0.23 in
Dimension - Pad Width inch	0.47 in
Dimension - Strip Length inch	5/16
Dimension - Stud Size inch	1/4

### Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	20
Packaging Type	Bag

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)