



YHSA14K6

by Burndy
Catalog ID: YHSA14K6

Cu Heat Shrink Terminal, Ring Tongue, 14-16 AWG, #4-6 Stud, 1.18" L, 0.30" W, Serrated bbl, Tin plated, Blue(Insul Color).

Features: Made From Pure Copper, Annealed For Maximum Strength, Color-Coded, Imprinted With Wire Size, Serrated Barrels Offer Maximum Wire Contact And Tensile Strength, Electro Tin Plated For Corrosion Resistance, Wire Strip Length 5/16 IN, Finish: Electro-Tin Plated, Wire Strip Length: 5/16 IN, Package: 100/Bag

Product Details

General

Application	For Use On Copper Conductor
Connector Type	Terminal
Physical Attribute - Tongue Type	Ring
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810524787
UPC 12 Digit	7818105247877

Dimensions

Dimension - B Length inch	0.22 in
Dimension - Hole Size inch	0.14 in
Dimension - Hole Size mm	4 mm
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.15 in
Dimension - Pad Width inch	0.30 in
Dimension - Strip Length inch	5/16
Dimension - Stud Size inch	#6

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)