

YHSA18K10FRK

by Burndy
Catalog ID: YHSA18K10FRK

Heat Shrink Fork Tongue Terminal For 22 - 18 AWG and #10 Stud.



Product Details

General

| | |
|--------------------------------------|--------------|
| Connector Type | Terminal |
| Insulation | Y |
| Insulation Type | Heat Shrink |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Fork |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | HYDENT™ |
| UPC | 781810477335 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length fraction | 2/9 in |
| Dimension - B Length inch | 0.22 in |
| Dimension - Hole Size fraction | 1/5 |
| Dimension - Hole Size inch | 0.20 in |
| Dimension - Hole Size mm | 5 mm |
| Dimension - L Length Overall mm | 30 mm |
| Dimension - Length Overall inch | 1.18 in |
| Dimension - N inch | 0.27 in |
| Dimension - Pad Width inch | 0.31 in |
| Dimension - Strip Length inch | 5/16 |
| Dimension - Stud Size inch | #10 |

Conductor Related

| | |
|----------------|--|
| Conductor Type | <ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size |
|----------------|--|

Certifications and Compliance

| | |
|-------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |

| | |
|------------------------------------|----|
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|--------|
| Carton Quantity | 100 EA |
| Minimum Pack Quantity | 20 |
| Packaging Type | Bag |

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)