

YHSMQ18M18X02D

by Burndy
Catalog ID: YHSMQ18M18X02D

Cu Heat Shrink Fully Insul Male Quick Disconnect, 18-22 AWG, 1.25" L, 0.18" W, Tin plated



Product Details

General

Connector Type	Male Disconnect
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810525418

Dimensions

Dimension - B Length fraction	8/74 in
Dimension - B Length inch	0.17 in
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.25 in
Dimension - Pad Width inch	0.18 in
Dimension - Strip Length inch	5/16 in

Conductor Related

Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)